


Anderson Greenwood Instrumentation Manifolds - Three Valve

A miniature three-valve manifold with the option of metal or soft seats for applications requiring remote mounting from the instrument

General Application

The MM1 is used to set or reset differential pressure switches during initial plant start-up or in assemblies for portable differential pressure test equipment used for any miniature differential pressure measuring device.



TECHNICAL DATA

Materials

CS, Brass, 316 SS, Hastelloy®

Seats:

Metal or soft

Connections:

Instrument: 1/4" NPT

Process: 1/4" NPT

Pressure (max):

6000 psig (414 barg)

Temperature range (min/max):

-70°C to 1000°F

(-57°C to 538°C)

Features


- Cost savings of 20-30% when manifolding by eliminating several parts used in conventional methods of 'piping up'.
- Compact design requires minimum space for operation and installation; ideal for installations behind boards and in cabinets.
- Fewer leak points reduce the chances of leakage.
- Unique valve seat can be converted from soft to hard simply by removing two insert washers.
- Rolled stem and bonnet threads increase strength and prevent galling, increasing valve life.
- Back seat stem feature prevents stem blowout.
- PTFE stem seal packing is easily adjusted for leak-proof and long service life.
- O-ring stem seal threads are isolated from process preventing galling and corrosion of the stem threads due to exposure to the process fluid.

MM1 SERIES

Anderson Greenwood Instrumentation Manifolds - Three Valve

MM1 Dimensions

Dimensions, inches (mm)



Dimensions, inches (mm)

Packing	A	B
O-ring	5.62 (142.7)	2.00 (50.8)
PTFE	6.82 (173.2)	2.60 (66.0)
Graphite	7.76 (197.1)	3.07 (78)

NOTE

1. Approximate valve weight: 1.0 lb (0.4 kg).
 0.136-inch (3.5 mm) diameter orifice.
 Valve Cv hard seat 0.25 maximum.
 Valve Cv soft seat 0.24 maximum.

Anderson Greenwood Instrumentation Manifolds - Three Valve

Bonnet Assembly Options

The MM1 features mini-valve bonnet assemblies, with a compact design and a one-piece rotating stem which is ‘V’ tipped with a shoulder for use as a metal or soft seated valve. The stem threads are rolled and lubricated to prevent galling and reduce operating torque. All miniature manifolds and valves feature a unique valve seat which may be converted from soft to metal simply by removing two insert washers.

The mini-valve bonnets come in two designs:

- An adjustable PTFE stem packed bonnet which is suitable for panel mounting via external bonnet threads.
- O-ring bonnet assemblies which use a NBR or FKM O-ring seal below the stem thread.

Standard Materials

Valve	Body	Bonnet	Stem	Flow washer ⁴⁾
CS ¹⁾	A108	A108	A581-303	316
Brass	B16	B16	A581-303	316
316 SS	A276-316	A479-316	A276-316	316
SG ³⁾	A276-316	A479-316	Monel [®] R405	316
SG3 ⁵⁾	Hastelloy [®] C276	Hastelloy [®] C276	Hastelloy [®] C276	Hastelloy [®] C276

Minimum Temperature

Carbon steel	-20°F (-29°C)
Brass and 316 SS O-ring seal	-20°F (-29°C)
316 SS, Monel [®] , Hastelloy [®]	-70°F (-57°C)
PTFE packed	
Delrin [®] Seat	-40°F (-40°C)
316 SS, Monel [®] , Hastelloy [®]	-70°F (-57°C)
Graphite packed	

Pressure and Temperature ratings⁶⁾

Seat	PTFE bonnet		Graphite bonnet ⁷⁾
	CS and SS valves	Brass valves	SS valves
Hard	6000 psig at 200°F (414 barg at 93°C)	3000 psig at 400°F (207 barg at 204°C)	6000 psig at 200°F (414 barg at 93°C)
	4000 psig at 500°F (276 barg at 260°C)		1500 psig at 1000°F (103 barg at 538°C)
Delrin [®] and PCTFE ²⁾	3000 psig at 200°F (207 barg at 93°C)	3000 psig at 200°F (207 barg at 93°C)	
PEEK	6000 psig at 200°F (414 barg at 93°C)	3000 psig at 300°F (207 barg at 149°C)	
	3000 psig at 300°F (207 barg at 149°C)		
O-ring bonnet			
Hard	6000 psig at 200°F (414 barg at 93°C)	3000 psig at 200°F (207 barg at 93°C)	
Delrin [®] and PCTFE ²⁾	3000 psig at 200°F (207 barg at 93°C)	3000 psig at 200°F (207 barg at 93°C)	
PEEK	6000 psig at 200°F (414 barg at 93°C)	3000 psig at 200°F (207 barg at 93°C)	


NOTES

1. CS is zinc TCP plated to prevent corrosion.
2. PCTFE (Polychlorotrifluoroethylene) is the exact equivalent of Kel-F[®].
3. SG (Sour Gas) meets the requirements of NACE MR0175/ISO 15156 (for Chloride conditions ≤ 50 mg/l [ppm]) and NACE MR0103.
4. Soft seated valves only.
5. SG3 (Sour Gas) meets the requirements of NACE MR0175/ISO 15156 (for Chloride conditions > 50 mg/l [ppm]).
6. Pressure and temperature ratings are not shown on valve body.
7. Graphite packed bonnet comes complete with ball end stem; 316 SS only. 1000°F (538°C)


MM1 SERIES

Anderson Greenwood Instrumentation Manifolds - Three Valve


Pressure vs. Temperature



Pressure vs. Temperature - Brass valves



Pressure vs. Temperature - SS valves with Graphite bonnet



NOTES

- (V or H) = with PTFE or Graphite bonnet assemblies.
- (R) = with O-ring bonnet assembly.
- PCTFE (Polychlorotrifluoroethylene) is the exact equivalent of Kel-F[®].

Anderson Greenwood Instrumentation Manifolds - Three Valve

Selection Guide

MM1	V	D	S	-2	-SG
BASIC SERIES	PACKING	SEAT	BODY MATERIAL	CONNECTION	OPTIONS ⁽¹⁾
MM1	V PTFE	D Delrin®	C CS, A108	2 1/4-inch FNPT	SG (Sour Gas) meets the requirements of NACE MR0175/ISO 15156 (for chloride conditions ≤ 50 mg/l (ppm)) and NACE MR0103-2005 SG3 (Sour Gas) Meets the requirements of NACE MRO175/ISO15156 (for chloride conditions > 50 mg/l (ppm)) Hastelloy Material used for all wetted materials
	R O-ring	K PCTFE (Polychlorotrifluoroethylene) is the exact equivalent of Kel-F®	B Brass B16		
	H Graphite (SS only) 1000°F (538°C) max	E PEEK	S 316 SS, A276-316		
		I Integral (body material)	J Hastelloy®		

NOTES

1. Not available with AGCO Mount kit.
2. Delrin® is a registered trademark of E.I. du Pont de Nemours and Company.
3. Hastelloy® is a registered trademark of Haynes International, Inc.
4. Kel-F® is a registered trademark of 3M Company.
5. Monel® is a registered trademark of the Special Metals Corporation.